


G4T




Compact with lever actuated contact.



The G4T plam handle, which is available in different versions, impresses with its simple, timeless design. Already in the basic version it has a front button, which is easy to operate thanks to the large, molded latch. Optionally, a second push-button, a rocker switch or a rotary

potentiometer can be installed at the top.

This handle is ideal for use on scissor lifts, work platforms, cranes, agricultural and forestry equipment where a lever actuated contact to control a machine is needed.

Versions		
G4T Handle with: Lever actuated momentary pushbutton 1NO Adapter for Spobu joysticks with 8 mm lever		
G4T-DT Handle with: Lever actuated momentary pushbutton 1NO Pushbutton on top 1NO Adapter for Spobu joysticks with 8 mm lever		
G4T-WT Handle with: Lever actuated momentary pushbutton 1NO Rocker switch on top, transversely installed, 1-0-1, 1 changeover contact Adapter for Spobu joysticks with 8 mm lever		
G4T-G10-GDLR55 Handle with: Lever actuated momentary pushbutton 1NO Rotary potentiometer on top, 5k-0-5k with direction signals, spring return in center position Adapter for Spobu joysticks with 8 mm lever		
Options		
Lever actuated monentary pushbutton with 1NO1NC contacts instead of 1NO		
Pushbutton 1NO 1NC instead of 1NO		
Special adapter		
Notes: Wiring: 1 m Teflon single cores AWG24.		
For the connection of the potentiometer GDLR55 it is essential to observe the notes on sheet TI-POTI-6.		

1) when mounted on Spobu joystick
• Notes on handle wiring and maximum number of cores, see sheet G-V.